

Product data sheet

Specifications



Thorsman - TML-E - joint cover piece - wall - beige

ISM18345

⚠ Discontinued on: Sep 26, 2017

⚠ End-of-service on: Oct 26, 2017

⚠ Discontinued

Main

| | |
|---------------------------|-------------------|
| Range Of Product | Thorsman |
| Product Name | Thorsman TML-E |
| Product Or Component Type | Joint cover piece |
| Colour Tint | Beige (RAL 1015) |
| Quantity Per Set | Set of 5 |

Complementary

| | |
|-------------------|---|
| Trunking Material | Plastic |
| Fixing Mode | Snap-fitted |
| Material | ABS (acrylonitrile butadiene-styrene) untreated |
| Length | 43 mm |
| Height | 78 mm |
| Width | 24 mm |

Environment

| | |
|---------------------------------------|---------------------------------------|
| Standards | EN 50085-1:1997/A1 EN 50085-1:1998 |
| Ambient Air Temperature For Operation | -20...60 °C |
| Ip Degree Of Protection | IP40 |

Packing Units

| | |
|------------------------------|-------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 3.6 g |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications