

Product data sheet

Specifications



OptiLine 45 - pole - tension-mounted - two-sided - white - 3100-3500 mm

ISM20109

⚠ Discontinued on: May 30, 2017

⚠ End-of-service on: Feb 6, 2018

⚠ Discontinued

Main

Range	OptiLine
Product Name	OptiLine 45
Cabling Installation System	Pole
Product Type	Pole
Type Of Pole	Two-sided
Pole/Post Surface Finish	Powder coated
Pole Fixing Mode	Tension-mounted

Complementary

Additional Information	Adjustability of ceiling fixing 400 mm
Colour	White (RAL 9010)
Front Opening Size	45 mm
Material	Aluminium powder coated
Quantity Package 1 / Unit	Set of 1
Height	3100...3500 mm
Depth	90 mm
Width	116 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP30

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.6 cm
Package 1 Width	350 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	9 cm
Package 1 Weight	12.365 kg

Contractual warranty

Warranty	18 months
----------	-----------