



Main

| | |
|-----------------------------|-------------|
| Range of product | OptiLine 45 |
| Cabling installation system | Service box |
| Product type | Service box |
| Type of service box | Basic |
| Configuration | Empty |

Complementary

| | |
|---------------------------|--------------------|
| Colour | Natural |
| Number of modules | 6 modules |
| Material | Aluminium anodized |
| Quantity package 1 / unit | 1 piece |
| Length | 330 mm |
| Height | 60 mm |
| Width | 60 mm |

Environment

| | |
|-------------------------|------------|
| Operating temperature | -5...60 °C |
| IP degree of protection | IP30 |

Offer Sustainability

| | |
|--------------------------|---|
| Sustainable offer status | Green Premium product |
| RECh Regulation | RECh Declaration |
| RECh free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |

| | |
|----------------------------|---|
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |