

Product data sheet

Specifications



OptiLine 70 - pole with 1 box - tension-mounted - natural - 5100-5500 mm

ISM20513

⚠ Discontinued on: Feb 22, 2017

⚠ Discontinued

Main

Range	OptiLine
Product Name	OptiLine 70
Cabling Installation System	Pole
Product Type	Pole
Type Of Pole	One installation box
Pole/Post Surface Finish	Anodized
Pole Fixing Mode	Tension-mounted

Complementary

Additional Information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front Opening Size	70 mm
Material	Aluminium anodized
Quantity Package 1 / Unit	Set of 1
Height	5100...5500 mm
Width	90 mm

Environment

Standards	73/23/EEC 93/68/EEC IEC 1084-2-4 SS 424 10 32 EN-AW-6063
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP40

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	9810 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

