

# Product data sheet

Specifications

## OptiLine 45 - swivel fixing



ISM50823

### Main

Range	OptiLine
Cabling Installation System	Floor box
Product Type	Swivel fixing
Type Of Floor	Raised floor
Floor Box Shape	Square Rectangular
Colour	Blue (RAL 5003)
Quantity Package 1 / Unit	2 pieces

### Complementary

Suitable For	For floor outlet box
Number Of Modules	Without modules
Product Material	PA6 Steel
Length	25 mm
Height	58 mm
Width	12 mm

### Environment

Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	2.5 cm
Package 1 Length	5 cm
Package 1 Weight	5 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	2
Package 2 Height	2 cm
Package 2 Width	17 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	17 cm
Package 2 Weight	27 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	100
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.01 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



## Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations