

Product data sheet

Specifications



Thorsman Glands - cable gland - grey - M20 - diameter 6 to 12

ISM71503

Main

| | |
|----------------------|-----------------|
| Product Range | Thorsman Glands |
| Product Type | Cable gland |
| Colour | Grey (RAL 7035) |
| Quantity Per Package | Set of 20 |

Complementary

| | |
|----------------------|-----------|
| Material | PA6 |
| Iso Thread | M20 |
| Cable Outer Diameter | 6...12 mm |

Environment

| | |
|-----------------------|--|
| Ip-Class | IP68 |
| Operating Temperature | -30...80 °C permanently -30...150 °C intermittently |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.0 cm |
| Package 1 Width | 18.5 cm |
| Package 1 Length | 32.0 cm |
| Package 1 Weight | 13.0 g |
| Unit Type Of Package 2 | BAG |
| Number Of Units In Package 2 | 20 |
| Package 2 Height | 20.0 cm |
| Package 2 Width | 20.0 cm |
| Package 2 Length | 4.0 cm |
| Package 2 Weight | 263.0 g |
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 8000 |
| Package 3 Height | 73.0 cm |
| Package 3 Width | 100.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|-----------|
| Package 3 Length | 120.0 cm |
| Package 3 Weight | 124.86 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | | |
|-----------------------|----------------------------|---|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | | REACH Declaration |
| | | |
| Eu Rohs Directive | | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| | | |
| China Rohs Regulation | | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |