

# Product data sheet

Specifications



## Thorsman Glands - cable gland - grey - M40 - diameter 19 to 28

ISM71506

### Main

Product Range	Thorsman Glands
Product Type	Cable gland
Colour	Grey (RAL 7035)
Quantity Per Package	Set of 5

### Complementary

Material	PA6
Iso Thread	M40
Cable Outer Diameter	19...28 mm

### Environment

Ip-Class	IP68
Operating Temperature	-30...80 °C permanently -30...150 °C intermittently

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	5.5 cm
Package 1 Length	5.3 cm
Package 1 Weight	58 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	5
Package 2 Height	16 cm
Package 2 Width	16 cm
Package 2 Length	17 cm
Package 2 Weight	340 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	200
Package 3 Height	37 cm
Package 3 Width	37 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Length	56 cm
Package 3 Weight	12.2 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)