



ⓘ Discontinued

KB113LS has not been replaced. Please contact your customer care center for more information.

Main

Range	Vivace
Product or component type	Socket-outlet with switch
Device short name	KB113
Device presentation	Complete mechanism

Complementary

Pilot light	Red neon indicator
Outlet poles configuration	2P + E
Number of gangs	1 gang
Colour tint	White
Material	Polycarbonate (grid plate) Polycarbonate (surround) Polycarbonate (base)
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	13 A at 250 V AC, no inductive load
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	Earth L N
Tightening torque	0.4 N.m
Clamping connection capacity	3 x 2.5 mm ² 2 x 4 mm ²

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	86 mm
Height	86 mm

Environment

Standards	IEC 60884
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------