



### Main

Range	Vivace
Product or component type	Switch
Device short name	KB31
Device application	Control
Device presentation	Complete mechanism

### Complementary

Switch function	Intermediate
Actuator	Rocker
Number of gangs	1 gang
Colour tint	White
Material	Polycarbonate (grid plate) Polycarbonate (surround) Nylon (base)
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	10 A at 250 V AC, fluorescent
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	L1 L2
Tightening torque	0.4 N.m
Clamping connection capacity	$\leq 2.5 \text{ mm}^2$

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	86 mm
Height	86 mm

## Environment

Standards	IEC 60669-1 MS IEC 60669-1 SS 227
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1110 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------