



Main

Product or component type	Socket-outlet
Device short name	KB426
Device presentation	Complete mechanism
Outlet standard	Schuko
Colour tint	White

Complementary

Outlet poles configuration	2 x 2P + E with shutters
Number of gangs	1 gang
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	13 A at 250 V AC, resistive 13 A at 250 V AC, inductive
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	N L E
Tightening torque	0.4 N.m
Clamping connection capacity	2.5 mm ²
Width	86 mm
Height	86 mm

Environment

Standards	IEC 60884
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Contractual warranty

Warranty	18 months
----------	-----------