

Product data sheet

Specifications



15A 250V 1 Gang Socket

KB426_15

⚠ Discontinued on: Jun 24, 2016

⚠ End-of-service on: Sep 26, 2016

⚠ Discontinued

Main

Product Or Component Type	Socket-outlet
Device Short Name	KB426
Device Presentation	Complete mechanism
Colour Tint	White

Complementary

Outlet Poles Configuration	2P + E
Number Of Gangs	1 gang
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	35 mm
Rated Current	15 A at 250 V AC, inductive
Network Frequency	50 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Pillar terminal
Terminal Identifier	L E N
Tightening Torque	0.4 N.m
Clamping Connection Capacity	<= 2.5 mm²
Width	86 mm
Height	86 mm

Environment

Standards	BS 546
Ambient Air Temperature For Operation	-5...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	0...95 %
Environmental Characteristic	Indoor use

Contractual warranty

Warranty	18 months
----------	-----------