



Main

Range	Canalis
Product or component type	Tap-off unit
Device short name	KBC
Product compatibility	KDP KBB KBA
Device application	Lighting
Range compatibility	Canalis KBA Canalis KBB Canalis KDP

Complementary

[Ue] rated operational voltage	230...240 V
[Ui] rated insulation voltage	690 V
[Ie] rated operational current	10 A at 35 °C
Network frequency	50/60 Hz
Protection type	Without protection
Electrical connection	Pre-wired with SO5Z1Z1-F - 3 x 1.5 mm ² - 0.8 m long
Busbar trunking polarity	L2 + L1 + L3 + N + PE L1 + N + PE
Tap-off unit polarity	L3+N
Tap-off unit connector type	With fixed polarity
Tap-off lock colour	Brown
Standards	EN/IEC 61439-6 EN/IEC 60439-2
Width	55 mm
Depth	12.5 mm
Height	42 mm
Colour	RAL 9001 : cream

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product weight	100 g
Quantity per set	Set of 10

Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1010 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------