



has not been replaced. Please contact your customer care center for more information.

### Main

Range of product	Vivace
Device short name	KBE34
Product or component type	Switch
Device presentation	Complete mechanism
Switch application	Switch

### Complementary

Switch function	1-way
Actuator	Small dolly rocker
Number of gangs	4 gangs
Colour tint	White
Material	Polycarbonate: surround Polycarbonate: grid plate Polycarbonate: dolly Nylon: base
Projecting depth	8.5 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	10 AX at 250 V AC, fluorescent load 10 A at 250 V AC, resistive load
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Contacts material	Brass Brass and silver inlay
Connections - terminals	Pillar terminal
Terminal identifier	L COM
Tightening torque	0.4 N.m
Clamping connection capacity	2 x 1.5 mm <sup>2</sup> 1 x 4 mm <sup>2</sup>
Width	86 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

Height	86 mm
--------	-------

---

## Environment

---

Standards	MS IEC 60669-1 IEC 60669-1
Product certifications	JKR
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Operating altitude	<= 2000 m
IP degree of protection	IP20

---

## Contractual warranty

---

Warranty	18 months
----------	-----------

---