



Main

Range of product	Harmony Series K
Product or component type	Cam switch operating head
Component name	KDD
Product compatibility	Front mounting bodies 12 and 20 A by Ø 22 mm hole
Cam switch head type	With front plate 60 x 60 mm
Type of operator	Black handle, length = 42 mm
Rotary handle padlocking	Without
Presentation of legend	Without

Complementary

Mechanical durability	1000000 cycles
CAD overall width	60 mm
CAD overall height	60 mm
CAD overall depth	77 mm
Length	42 mm
Product weight	0.053 kg

Environment

Protective treatment	TC
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Shock resistance	30 gn conforming to IEC 68-2-27
Vibration resistance	5 gn, 10...150 Hz conforming to IEC 68-2-6
IP degree of protection	IP65 conforming to IEC 529 IP65 conforming to NF C 20-010

Contractual warranty

Warranty period	18 months
-----------------	-----------