



Main

Range of product	Canalis
Range compatibility	Canalis KT Canalis KH
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KT busbar trunking with KH type plug-in outlets Canalis KHF and KGF busbar trunking with plug-in outlets
[Ie] rated operational current	400 A
Protection type	Fupact INF switch-disconnector fuse : for DIN fuse, size 2 - 400 A - conforming to DIN 43653 standard
Provided equipment	Switch-disconnector
Mounting mode	Plug-in with auto-clamping system
Tap-off unit polarity	3L+N+PE

Complementary

Device application	Medium power distribution
[Ue] rated operational voltage	690 V
[Uimp] rated impulse withstand voltage	8 kV
[Ui] rated insulation voltage	800 V
Network frequency	50/60 Hz
Control type	Rotary handle
Standards	IEC 61439-1 IEC 61439-6
Colour	White RAL 9001
Width	760 mm
Depth	590 mm
Height	569 mm

Environment

Earthing system	TT IT TN-S
IP degree of protection	IP43 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1418 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
