



Main

Range of product	Canalis
Range compatibility	Canalis KT Canalis KH
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KT busbar trunking with KH type plug-in outlets Canalis KHF and KGF busbar trunking with plug-in outlets
[Ie] rated operational current	400 A
Protection type	Fupact INF switch-disconnector fuse : for DIN fuse, size 2 - 400 A - conforming to DIN 43653 standard
Provided equipment	Switch-disconnector
Mounting mode	Plug-in with auto-clamping system
Tap-off unit polarity	3L+PEN

Complementary

Device application	Medium power distribution
[Ue] rated operational voltage	690 V
[Uimp] rated impulse withstand voltage	8 kV
[Ui] rated insulation voltage	800 V
Network frequency	50/60 Hz
Control type	Rotary handle
Standards	IEC 61439-1 IEC 61439-6
Colour	White RAL 9001
Width	760 mm
Depth	590 mm
Height	569 mm

Environment

Earthing system	TN-C
IP degree of protection	IP43 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1418 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations