



Main

Range of product	Canalis
Range compatibility	Canalis KT Canalis KH
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KT busbar trunking with KH type plug-in outlets Canalis KHF and KGF busbar trunking with plug-in outlets
[Ie] rated operational current	630 A
Protection type	Circuit breaker : NSX630
Provided equipment	Circuit breaker to be ordered separately
Mounting mode	Plug-in with auto-clamping system
Tap-off unit polarity	3L+PEN

Complementary

Device application	Motor
[Ue] rated operational voltage	220 V
Network frequency	50 Hz
Control type	Extended rotary handle
Door/Cover opening side	Down
Standards	IEC 61439-1 IEC 61439-6
Colour	White RAL 9001
Width	780 mm
Depth	275 mm
Depth (door open)	646 mm
Height	371 mm
Product weight	45 kg

Environment

Earthing system	TN-C
-----------------	------

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1418 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations