



Main

Range of product	Canalis
Range compatibility	Canalis KT Canalis KH
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KT busbar trunking with KH type plug-in outlets Canalis KHF and KGF busbar trunking with plug-in outlets
[Ie] rated operational current	1000 A
Protection type	Fuse isolator : for DIN fuse, size 4 - 1000 A
Provided equipment	Fuse to be ordered separately
Mounting mode	Plug-in with auto-clamping system
Tap-off unit polarity	3L+N+PE

Complementary

Device application	High power distribution
[Ue] rated operational voltage	690 V
[Uimp] rated impulse withstand voltage	8 kV
[Ui] rated insulation voltage	800 V
Network frequency	50/60 Hz
Electrical connection	Cable clamp terminal - cable : 185 mm ² (x4)
Standards	IEC 61439-1 IEC 61439-6
Colour	White RAL 9001
Width	650 mm
Depth	420 mm
Height	485 mm
Product weight	90 kg

Environment

Earthing system	TT
-----------------	----

IT
TN-S

IP degree of protection	IP31 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1418 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations