



Main

Range of product	Canalis
Product name	KN
Product or component type	Feed unit
BAR MATERIAL	Plastic
Product compatibility	KN
[Ie] rated operational current	40 A 63 A
Mounting location	Left Right
Colour	White : RAL 9001

Complementary

Protection type	Without protection
[Ue] rated operational voltage	230...500 V
Connections - terminals	Terminal block for 16 mm ² flexible Terminal block for 25 mm ² rigid
Control type	Without
Number of circuits	1
Provided equipment	End cover
Mounting mode	By clips
Mounting support	Busbar
Standards	IEC 60439-2 IEC 61439-6
Width	265 mm
Depth	71 mm
Height	92 mm
Product weight	580 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1012 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------