



### Main

Range of product	Canalis
Product name	KS
Product or component type	Electrical and mechanical jointing
Product compatibility	KS
[Ie] rated operational current	1000 A 800 A
Offer type	Spare part
Colour	White (RAL 9001)

### Complementary

Device application	Medium power distribution
[Ue] rated operational voltage	230...690 V
Control type	Without
Number of circuits	1
Busbar trunking polarity	3L + N + PE
Width	276 mm
Depth	117 mm
Height	167 mm
Net weight	4.5 kg

### Environment

IK degree of protection	IK08 conforming to IEC 62262
IP degree of protection	IP55 conforming to IEC 60529
Standards	IEC 61439-6 IEC 60439-2

### Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------

