



### Main

Range of product	Canalis
Product name	KS
Product or component type	Feed unit
BAR MATERIAL	Aluminium
Product compatibility	FL21 gland plate
[Ie] rated operational current	400 A
Mounting location	Central
Colour	White (RAL 9001)

### Complementary

Protection type	Without protection
[Ue] rated operational voltage	230...690 V
Connections - terminals	Lug for 240 mm <sup>2</sup> flexible Lug for 240 mm <sup>2</sup> rigid
Control type	Without
Number of circuits	1
Provided equipment	End cover
Mounting mode	By screws
Mounting support	Busbar
Standards	IEC 60439-2 IEC 61439-6
Width	688 mm
Depth	213.5 mm
Height	498 mm
Body material	Metal
Net weight	15.5 kg

### Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

IK degree of protection	IK08 conforming to IEC 62262
-------------------------	------------------------------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------

