

KT12BHC has not been replaced. Please contact your customer care center for more information.

# Legacy products

ⓘ Discontinued

## Main

Range of product	Profil
Product or component type	Printed circuit board
Additional information	With location for emergency stop unit and soldered adaptor
Device short name	KT
Installed device	12 dialogue units

## Complementary

Product destination	For Harmony XB4 and XB5 push-buttons, switches and pilot lights
[I <sub>e</sub> ] rated operational current	3 A at 30 V AC
Supply	Via connector
Electrical connection	Screw connector 1.5 mm <sup>2</sup>
Marking	CE
Product weight	0.312 kg

## Environment

Standards	IEC 60947-1 IEC 60947-5-1 UL 508 CSA C22.2 No 14
Product certifications	CSA UL
Electrical shock protection class	Class I fitted with XB4B units conforming to EN/IEC 61140 Class II fitted with XB5A units conforming to EN/IEC 61140
IP degree of protection	IP65
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn (f=10...500 Hz) conforming to IEC 60068-2-6 all units except mushroom head push-buttons 5 gn (f=10...500 Hz) conforming to IEC 60068-2-6 mushroom head push-buttons
Shock resistance	10 gn (duration=11 ms) conforming to IEC 60068-2-27 mushroom head push-buttons 50 gn (duration=11 ms) conforming to IEC 60068-2-27 all functions except mushroom head push-buttons

## Contractual warranty

Warranty period	18 months
-----------------	-----------