



Main

Range	C-Bus
Product or component type	Dimmer
Device application	Control
Load type	Minimum incandescent
Provided equipment	2 pole RCCB
Number of channels	6

Complementary

Leakage current	< 10 mA
[Us] rated supply voltage	240 V AC 47...53 Hz 415 V AC 47...53 Hz
Starting time	0.5 s
Rated breaking capacity	6 kA
[Ui] rated insulation voltage	500 V
Product weight	17.5 kg
Width	455 mm
Height	451 mm
Depth	164 mm

Environment

Dielectric strength	2500 V
Directives	2004/108/EC - electromagnetic compatibility 2002/95/EC - RoHS directive
Standards	EN 55014-1 EN 55015 EN 61000-3-2 EN 61000-3-3 IEC 60439-1 IEC 60669-2-1 AS/NZS CISPR 15 AS/NZS 3439-1 AS/NZS CISPR 14-1 EN 61000-3-5 EN 61000-3-11

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications