



Main

Range	C-Bus
Product or component type	Dimmer
Device application	Control
Load type	Minimum incandescent
Number of channels	6

Complementary

Leakage current	< 10 mA leading edge < 1 mA trailing edge
[Us] rated supply voltage	240 V AC 47...53 Hz 415 V AC 47...53 Hz
Starting time	0.5 s
Rated breaking capacity	6 kA
[Ui] rated insulation voltage	500 V

Environment

Dielectric strength	2500 V
Directives	2004/108/EC - electromagnetic compatibility 2002/95/EC - RoHS directive
Standards	EN 55014-1 EN 55015 EN 61000-3-2 EN 61000-3-3 IEC 60439-1 IEC 60669-2-1 AS/NZS CISPR 15 AS/NZS 3439-1 AS/NZS CISPR 14-1 EN 61000-3-5 EN 61000-3-11

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1204 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

