



Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	LC1D80...D150 (3P) LC1D80004...D115004 (4P) LC1D40008...D80008 (4P)

Complementary

Mounting location	Top
Mounting mode	By screws
Suppressor technology	RC circuit
[Uc] control circuit voltage	110...240 V AC 50/60 Hz
Maximum peak voltage	3 Uc
Product weight	0.018 kg

Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0805 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
