



### Main

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	LC1D09...D38 (3P) LC1DT20...DT40 (4P) LC1D098...D258 (4P) CAD32, CAD50

### Complementary

Mounting location	Side
Mounting mode	By clips
Suppressor technology	Flywheel diode
[Uc] control circuit voltage	24...250 V DC
Maximum peak voltage	1 Uc
Product weight	0.012 kg

### Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0725 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---