



### Main

Range	TeSys
Product name	TeSys F
Utilisation category	AC-4
Motor power kW	80 kW at 400 V AC (AC-4)

### Complementary

Standards	JIS C8201-4-1 IEC 60947-4-1 EN 60947-4-1 EN 60947-1 IEC 60947-1
Product certifications	CSA BV DNV UL RMRoS ABS RINA LROS (Lloyds register of shipping) CB CCC
Connections - terminals	Power circuit: bolted connection
Compatibility code	LC1F

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------