



Overview

Description	Automatic Voltage Regulator provides a standard level of voltage for various types of equipment with power requirements up to 1200 W or 1200 VA. Voltage is continuously transformed to the rated voltage of 220/230/240 V (depending on setting) with input voltage ranging from 160 to 300 V
Model Name	APC Line-R 1200VA Automatic Voltage Regulator, Schuko Outlets, 230V
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Algeria

Output

Output Power Capacity	1200 Watts / 1200 VA
Max Configurable Power (Watts)	1200 Watts / 1200 VA
Nominal Output Voltage	220V

Input

Nominal Input Voltage	220V
Input Frequency	47 - 63 Hz
Input Connections	Schuko CEE 7/7P
Cord Length	2 meters
Input voltage range for main operations	160 - 290V V
Input Breaker Capacity	8 A

Surge Protection and Filtering

Surge energy rating	300 Joules
---------------------	------------

Physical

Maximum Height	118.0 mm
Maximum Width	214.0 mm
Maximum Depth	148.0 mm
Net Weight	4.2 kg
Shipping Weight	4.2 kg

Shipping Height	176.0 mm
Shipping Width	273.0 mm
Shipping Depth	207.0 mm
Master Carton Units	4.0
Master Carton Weight	18.0 kg
SCC Codes	1073130429037 4
Units per Pallet	108.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Audible noise at 1 meter from surface of unit	0.000 dB

Conformance

Standard warranty	2 years repair or replace
-------------------	---------------------------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs