



### Overview

Model Name	Line-R 1200VA Automatic Voltage Regulator
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Aruba

### Output

Output Power Capacity	1200 Watts / 1200 VA
Max Configurable Power (Watts)	1200 Watts / 1200 VA
Nominal Output Voltage	120V

### Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Cord Length	1.98 meters

### Surge Protection and Filtering

Surge energy rating	680 Joules
---------------------	------------

### Physical

Maximum Height	116.0 mm
Maximum Width	214.0 mm
Maximum Depth	141.0 mm
Net Weight	4.41 kg
Shipping Weight	4.7 kg
Shipping Height	175.0 mm
Shipping Width	273.0 mm
Shipping Depth	207.0 mm
Master Carton Units	4.0

Master Carton Dimensions (Length x Width x Height)	16.73 inches
Master Carton Weight	19.55 kg
Color	Beige
SCC Codes	1073130419791 8
Units per Pallet	64.0

### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	0.000 dB

### Conformance

Approvals	FCC Part 15 Class B
Standard warranty	2 years repair or replace
Equipment protection policy	Lifetime : \$25000