



⚠ Discontinued

has not been replaced. Please contact your customer care center for more information.

### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE2K
Product or component type	Enclosed DOL reversing starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Reversing contactor
[Ie] rated operational current	9 A AC-3
Motor power kW	4 kW at 380/400 V AC 50/60 Hz 4 kW at 415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 2.2 kW at 220/230 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	9 A
[Uc] control circuit voltage	24 V AC 50/60 Hz
Control type	Push-button stop/reset red O Push-button start down arrow Push-button start up arrow

### Complementary

Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 ISO20 top 4 2 Pg 13 + 2 Pg 16 bottom 4 ISO20 bottom
Width	175 mm
Height	165 mm
Depth	146 mm
Net weight	1.08 kg

### Environment

Material	Polycarbonate
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 60529

Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

### Contractual warranty

Warranty	18 months
----------	-----------