



has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3D
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Star-delta contactors Mechanical interlock
Motor power kW	11 kW at 220 V AC 50/60 Hz 22 kW at 415 V AC 50/60 Hz 22 kW at 440 V AC 50/60 Hz 18.5 kW at 380/400 V AC 50/60 Hz
[Uc] control circuit voltage	110 V AC 50/60 Hz
Control type	Without

Complementary

Cable entry number	2 ISO20 top 2 ISO25 top 2 ISO32 top 2 ISO40 top 2 ISO20 bottom 2 ISO25 bottom 2 ISO32 bottom 2 ISO40 bottom
Width	186 mm
Height	348 mm
Depth	167 mm
Net weight	3.75 kg

Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1

Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty	18 months
----------	-----------
