



## Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3D
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Star-delta contactors Mechanical interlock Neutral terminal
Motor power kW	15 kW at 220 V AC 50/60 Hz 30 kW at 380/400 V AC 50/60 Hz 30 kW at 415 V AC 50/60 Hz 30 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	440 V AC 50/60 Hz
Control type	Push-button start green I Push-button stop/reset red O

## Complementary

Cable entry number	2 ISO20 top 2 ISO25 top 2 ISO32 top 2 ISO40 top 2 ISO20 bottom 2 ISO25 bottom 2 ISO32 bottom 2 ISO40 bottom
Width	186 mm
Height	348 mm
Depth	175.5 mm
Net weight	5.16 kg

## Environment

IP degree of protection	IP65 conforming to IEC 60529
-------------------------	------------------------------

IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

### Contractual warranty

Warranty	18 months
----------	-----------