



LE3D406Q7 has not been replaced. Please contact your customer care center for more information.

### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3D
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Sheet steel
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Star-delta contactors Fuse disconnecter
Motor power kW	18.5 kW at 220 V AC 50/60 Hz 37 kW at 380/400 V AC 50/60 Hz 37 kW at 415 V AC 50/60 Hz 37 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	380 V AC 50/60 Hz
Associated fuse rating	80 A 14 x 51 mm aM
Control type	Without

### Complementary

Cable entry number	1 ISO32 top 5 1 ISO32 + 2 ISO20 + 2 ISO25 bottom 1 Pg 29 top 5 1 Pg 29 + 2 Pg 13 + 2 Pg 21 bottom
Width	400 mm
Height	500 mm
Depth	218 mm
Net weight	16.9 kg

### Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

---

Warranty	18 months
----------	-----------

---