



has not been replaced. Please contact your customer care center for more information.

Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3D
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Sheet steel
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Star-delta contactors
Motor power kW	37 kW at 220 V AC 50/60 Hz 75 kW at 380/400 V AC 50/60 Hz 75 kW at 415 V AC 50/60 Hz 75 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	220 V AC 50/60 Hz
Control type	Push-button start green I Push-button stop/reset red O

Complementary

Cable entry number	1 Pg 36 top 1 ISO40 top 5 2 Pg 13 + 3 Pg 36 bottom 5 2 ISO20 + 3 ISO40 bottom
Width	400 mm
Height	400 mm
Depth	218 mm
Net weight	14 kg

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty	18 months
----------	-----------
