



has not been replaced. Please contact your customer care center for more information.

### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3D
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Sheet steel
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Star-delta contactors
Motor power kW	37 kW at 220 V AC 50/60 Hz 75 kW at 380/400 V AC 50/60 Hz 75 kW at 415 V AC 50/60 Hz 75 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	240 V AC 50 Hz
Control type	Push-button start green I Push-button stop/reset red O

### Complementary

Cable entry number	1 Pg 36 top 1 ISO40 top 5 2 Pg 13 + 3 Pg 36 bottom 5 2 ISO20 + 3 ISO40 bottom
Width	400 mm
Height	400 mm
Depth	218 mm
Net weight	14 kg

### Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

---

Warranty	18 months
----------	-----------

---