



## Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3F
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Sheet steel
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Star-delta contactors
Motor power kW	185 kW at 220 V AC 50/60 Hz 315 kW at 380 V AC 50/60 Hz 355 kW at 415 V AC 50/60 Hz 375 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	380 V AC 50/60 Hz
Control type	Push-button start green I Push-button stop/reset red O

## Complementary

Width	800 mm
Height	1000 mm
Depth	419 mm
Net weight	82 kg

## Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

## Contractual warranty

Warranty	18 months
----------	-----------