



### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE3K
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Star-delta contactors Mechanical interlock Neutral terminal
Motor power kW	4 kW at 220 V AC 50/60 Hz 7.5 kW at 380/400 V AC 50/60 Hz 7.5 kW at 415 V AC 50/60 Hz 7.5 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	220 V AC 50/60 Hz
Control type	Push-button start green I Push-button stop/reset red O

### Complementary

Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 ISO20 top 4 2 Pg 13 + 2 Pg 16 bottom 4 ISO20 bottom
Width	175 mm
Height	165 mm
Depth	146 mm
Net weight	1.46 kg

### Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C

---

Environmental characteristic	Standard environment
------------------------------	----------------------

---

**Contractual warranty**

---

Warranty	18 months
----------	-----------

---