



ⓘ Discontinued

has not been replaced. Please contact your customer care center for more information.

### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE4D
Product or component type	Enclosed DOL starter
Device application	Standard
Material	Sheet steel
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Contactor Fuse disconnecter Neutral terminal
[Ie] rated operational current	40 A AC-3
Motor power kW	11 kW at 220/230 V AC 50/60 Hz 22 kW at 415 V AC 50/60 Hz 22 kW at 440 V AC 50/60 Hz 22 kW at 500 V AC 50/60 Hz 30 kW at 660/690 V AC 50/60 Hz 18.5 kW at 380/400 V AC 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	40 A
Associated fuse rating	40 A 14 x 51 mm aM
Control type	Push-button start green I Push-button stop/reset red O

### Complementary

Cable entry number	2 1 Pg 13 + 1 Pg 21 top 2 1 ISO20 + 1 ISO25 top 3 1 Pg 13 + 2 Pg 21 bottom 3 1 ISO20 + 2 ISO25 bottom
Width	367 mm
Height	195 mm
Depth	201 mm
Net weight	5.77 kg

## Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

## Contractual warranty

Warranty	18 months
----------	-----------