



### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE4K
Product or component type	Enclosed DOL starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Fuse disconnecter Contactor
[Ie] rated operational current	6 A AC-3
Motor power kW	3 kW at 440 V AC 50/60 Hz 1.5 kW at 220/230 V AC 50/60 Hz 2.2 kW at 380/400 V AC 50/60 Hz 2.2 kW at 415 V AC 50/60 Hz
[Uc] control circuit voltage	230 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	6 A
Associated fuse rating	10 A 10 x 38 mm aM
Control type	Without

### Complementary

Cable entry number	4 cable entry : 2 Pg 13 + 2 Pg 16 top 4 cable entry : 2 Pg 13 + 2 Pg 16 bottom 4 cable entry : ISO20 top 4 cable entry : ISO20 bottom
Width	175 mm
Height	165 mm
Depth	146 mm
Product weight	1.45 kg

### Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 60529

Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

### Contractual warranty

Warranty period	18 months
-----------------	-----------