



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE6D
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Fuse disconnecter Star-delta contactors Mechanical interlock
Motor power kW	11 kW at 380/400 V AC 50/60 Hz 11 kW at 415 V AC 50/60 Hz 11 kW at 440 V AC 50/60 Hz 5.5 kW at 220 V AC 50/60 Hz
[Uc] control circuit voltage	115 V AC 50/60 Hz
Associated fuse rating	25 A 10 x 38 mm aM
Control type	Push-button reset blue R

Complementary

Width	186 mm
Height	348 mm
Depth	175.5 mm
Product weight	3.9 kg

Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty period	18 months
-----------------	-----------
