



LE6D12P7A04 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

## Main

Range	TeSys
Product name	TeSys LE
Device short name	LE6D
Product or component type	Enclosed star-delta starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Fuse disconnecter Star-delta contactors Mechanical interlock
Motor power kW	11 kW at 380/400 V AC 50/60 Hz 11 kW at 415 V AC 50/60 Hz 11 kW at 440 V AC 50/60 Hz 5.5 kW at 220 V AC 50/60 Hz
[Uc] control circuit voltage	230 V AC 50/60 Hz
Associated fuse rating	25 A 10 x 38 mm aM
Control type	Without

## Complementary

Width	186 mm
Height	348 mm
Depth	167 mm
Product weight	3.9 kg

## Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---