



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE8K
Product or component type	Enclosed DOL reversing starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Reversing contactor Fuse disconnecter
[Ie] rated operational current	6 A AC-3
Motor power kW	3 kW at 440 V AC 50/60 Hz 1.5 kW at 220/230 V AC 50/60 Hz 2.2 kW at 380/400 V AC 50/60 Hz 2.2 kW at 415 V AC 50/60 Hz
[Uc] control circuit voltage	42 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	6 A
Associated fuse rating	10 A 10 x 38 mm aM
Control type	Push-button reset blue R

Complementary

Cable entry number	4 cable entry : 2 Pg 13 + 2 Pg 16 top 4 cable entry : 2 Pg 13 + 2 Pg 16 bottom 4 cable entry : ISO20 top 4 cable entry : ISO20 bottom
Width	175 mm
Height	165 mm
Depth	146 mm
Product weight	1.6 kg

Environment

IP degree of protection	IP65
IK degree of protection	IK09 conforming to IEC 60529

Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty period	18 months
-----------------	-----------