



Main

Range	TeSys
Product name	TeSys LG
Device short name	LG7K
Product or component type	Enclosed DOL starter
Device application	Safety
Utilisation category	AC-3
Device composition	Circuit-breaker Contactor
Motor power kW	0.06 kW at 220/230 V AC 50/60 Hz 0.09 kW at 400/415 V AC 50/60 Hz 0.12 kW at 440 V AC 50/60 Hz
Thermal protection adjustment range	0.25...0.4 A
[Uc] control circuit voltage	12 V AC 50/60 Hz
Control type	Mushroom head push-button emergency stop red

Complementary

Cable entry number	4 cable entry : 2 Pg 13 + 2 Pg 16 top 4 cable entry : 2 Pg 13 + 2 Pg 16 bottom
Width	175 mm
Height	165 mm
Depth	177 mm
Product weight	1.3 kg

Environment

Standards	IEC 60204-1 IEC 60947-4-1
Material	Polycarbonate
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Environmental characteristic	Standard environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
