



Main

Range	TeSys
Product name	TeSys LG
Device short name	LG7K
Product or component type	Enclosed DOL starter
Device application	Safety
Utilisation category	AC-3
Device composition	Circuit-breaker Contactor
Motor power kW	3 kW at 440 V AC 50/60 Hz 1.1 kW at 220/230 V AC 50/60 Hz 2.2 kW at 400/415 V AC 50/60 Hz
Thermal protection adjustment range	4...6.3 A
[Uc] control circuit voltage	220/230 V AC 50/60 Hz
Control type	Push-button start white I Push-button stop black O Mushroom head push-button emergency stop red

Complementary

Cable entry number	4 cable entry : 2 Pg 13 + 2 Pg 16 top 4 cable entry : 2 Pg 13 + 2 Pg 16 bottom
Width	175 mm
Height	165 mm
Depth	177 mm
Product weight	1.3 kg

Environment

Standards	IEC 60947-4-1 IEC 60204-1
Material	Polycarbonate
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Environmental characteristic	Standard environment

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0832 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
