



Main

Range	TeSys
Product name	TeSys LG
Device short name	LG7K
Product or component type	Enclosed DOL starter
Device application	Safety
Utilisation category	AC-3
Device composition	Circuit-breaker to be ordered separately Contactor
[Ie] rated operational current	6 A AC-3
[Uc] control circuit voltage	380/400 V AC 50/60 Hz
Control type	Push-button start white I Push-button stop black O Mushroom head push-button emergency stop red

Complementary

Cable entry number	4 cable entry : 2 Pg 13 + 2 Pg 16 top 4 cable entry : 2 Pg 13 + 2 Pg 16 bottom
Width	175 mm
Height	165 mm
Depth	177 mm
Product weight	1.3 kg

Environment

Standards	IEC 60204-1 IEC 60947-4-1
Material	Polycarbonate
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Environmental characteristic	Standard environment

Offer Sustainability

RoHS (date code: YYWW)	Compliant
------------------------	-----------

 Schneider Electric declaration of conformity

REACH

Reference not containing SVHC above the threshold
Reference not containing SVHC above the threshold

Contractual warranty

Warranty period

18 months
