



Main

| | |
|-------------------------------------|--|
| Range | TeSys |
| Product name | TeSys LG |
| Device short name | LG7K |
| Product or component type | Enclosed DOL starter |
| Device application | Safety |
| Utilisation category | AC-3 |
| Device composition | Circuit-breaker Contactor |
| Motor power kW | 0.06 kW at 220/230 V AC 50/60 Hz 0.09 kW at 400/415 V AC 50/60 Hz 0.12 kW at 440 V AC 50/60 Hz |
| Thermal protection adjustment range | 0.25...0.4 A |
| [Uc] control circuit voltage | 500 V AC 50/60 Hz |
| Control type | Mushroom head push-button emergency stop red |

Complementary

| | |
|--------------------|---|
| Cable entry number | 4 cable entry : 2 Pg 13 + 2 Pg 16 top 4 cable entry : 2 Pg 13 + 2 Pg 16 bottom |
| Width | 175 mm |
| Height | 165 mm |
| Depth | 177 mm |
| Product weight | 1.3 kg |

Environment

| | |
|------------------------------|------------------------------|
| Standards | IEC 60204-1 IEC 60947-4-1 |
| Material | Polycarbonate |
| IP degree of protection | IP55 conforming to IEC 60529 |
| IK degree of protection | IK07 conforming to IEC 60529 |
| Environmental characteristic | Standard environment |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
