



### Main

|                                     |  |
|-------------------------------------|--|
| Range                               | TeSys  |
| Product name                        | TeSys LG   |
| Device short name                   | LG8K   |
| Product or component type           | Enclosed DOL reversing starter   |
| Device application                  | Safety   |
| Utilisation category                | AC-3   |
| Device composition                  | Reversing contactor<br>Circuit-breaker                                   |
| Motor power kW                      | 0.18 kW at 400/415 V AC 50/60 Hz<br>0.18 kW at 440 V AC 50/60 Hz         |
| Thermal protection adjustment range | 0.4...0.63 A   |
| [Uc] control circuit voltage        | 42 V AC 50/60 Hz   |
| Control type                        | Selector switch 2 positions start black I-II<br>Push-button stop black O |

### Complementary

|                    |   |
|--------------------|---|
| Cable entry number | 4 cable entry : 2 Pg 13 + 2 Pg 16 top<br>4 cable entry : 2 Pg 13 + 2 Pg 16 bottom |
| Width              | 175 mm  |
| Height             | 165 mm  |
| Depth              | 146 mm  |
| Product weight     | 1.64 kg   |

### Environment

|                              |  |
|------------------------------|--|
| Standards                    | IEC 60204-1<br>IEC 60947-4-1               |
| Material                     | Polycarbonate                              |
| IP degree of protection      | IP55 for enclosure conforming to IEC 60529 |
| IK degree of protection      | IK07 conforming to IEC 60529               |
| Environmental characteristic | Standard environment                       |

Contractual warranty

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---