



### Main

Range	TeSys
Product name	TeSys LG
Device short name	LG8K
Product or component type	Enclosed DOL reversing starter
Device application	Safety
Utilisation category	AC-3
Device composition	Reversing contactor Circuit-breaker Padlocking device
Motor power kW	0.12 kW at 220/230 V AC 50/60 Hz 0.25 kW at 400/415 V AC 50/60 Hz 0.25 kW at 440 V AC 50/60 Hz
Thermal protection adjustment range	0.63...1 A
[Uc] control circuit voltage	48 V AC 50/60 Hz
Control type	Selector switch 2 positions start black I-II Push-button stop black O Mushroom head push-button emergency stop red

### Complementary

Cable entry number	4 cable entry : 2 Pg 13 + 2 Pg 16 top 4 cable entry : 2 Pg 13 + 2 Pg 16 bottom
Width	175 mm
Height	165 mm
Depth	146 mm
Product weight	1.64 kg

### Environment

Standards	IEC 60204-1 IEC 60947-4-1
Material	Polycarbonate
IP degree of protection	IP55 for enclosure conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Environmental characteristic	Standard environment

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---