

Product data sheet

Specifications



panel GLASS TOUCH PANELS for hotels - modbus - 4 buttons - sample order

LSSMBU04NS

Main

Product Name	Glass Touch Panels
Product Type	Configurable touchscreen panel
Device Application	Hotel Remote control Lighting Monitoring Energy efficiency Bell switch Ventilation
Color Buttons Display Options	Champagne gold White Silver Black
Colour Tint	Panel: black Panel: white Panel: silver Panel: champagne gold Button: white Button: amber Button: blue Button: light green Button: red Button: grey
Module Configuration	Configured with the Glass Touch Panel Design tool

Complementary

Control Button Type	4 configurable touch button
Local Signalling	configurable
[Us] Rated Supply Voltage	24 V DC
Current Consumption	30 mA
Communication Port Protocol	Modbus serial with RS485 port(s)
Mounting Mode	Magnetic Snap-in
Height	105 mm (standard) 95 mm (optional)
Width	105 mm (standard) 95 mm (optional)
Depth	33 mm (standard) 33 mm (optional)
Relative Humidity	10...95 %, non-condensing (operation)
Order Type	Mockup sample order

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient Air Temperature For Storage	0...60 °C
Ambient Air Temperature For Operation	0...45 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	13.5 cm
Package 1 Length	18.5 cm
Package 1 Weight	300.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.0 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	480
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	183.0 kg