


# Product data sheet

Specifications



trip unit TM63G for ComPact NSX  
100/160/250 circuit breakers,  
thermal magnetic, rating 63 A, 3  
poles 3d

LV429152

! Discontinued

! Discontinued on: Oct 26, 2023

**Important message:** This product has been switched to new ComPacT range and is no longer commercialized. It will continue to be available in H1 2023 only limited to specific projects.

## Main

Range	ComPact
Range Of Product	ComPact NSX100...250 ComPact NSX100...250 DC
Product Or Component Type	Trip unit
Trip Unit Name	TM-G
Trip Unit Technology	Thermal-magnetic
Range Compatibility	ComPact NSX100 ComPact NSX160 ComPact NSX100 DC
Device Application	Generator
Number Of Poles	3P
Protected Poles Description	3t
Trip Unit Protection Functions	LI
Protection Type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip Unit Rated Current	63 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz 750 V DC
Network Type	AC DC
Network Frequency	50/60 Hz

## Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.7...1 x In
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Tr] Long-Time Protection Delay Adjustment Range	120...400 s at 1.5 x In
Short-Time Protection Pick-Up Adjustment Type Isd	Fixed
[Isd] Short-Time Protection Pick-Up Adjustment Range	125 A
Short-Time Protection Delay Adjustment Type Tsd	Fixed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Earth-Leakage Protection	Without
--------------------------	---------

## Environment

Standards	EN/IEC 60947-2 UL 508
Product Certifications	CCC EAC Marine
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	9.6 cm
Package 1 Length	11.0 cm
Package 1 Weight	441.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	28
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	12.835 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>